

Picture Tube

BI-PANEL RECTANGULAR GLASS TYPE
LOW-VOLTAGE ELECTROSTATIC FOCUS

ALUMINIZED SCREEN
114° MAGNETIC DEFLECTION

With Heater Having Controlled Warm-Up Time

GENERAL DATA

Electrical:

Heater Current at 6.3 volts.	600 ± 5%	ma
Heater Warm-Up Time (Average).	11	seconds
Direct Interelectrode Capacitances:		
Grid No.1 to all other electrodes. . .	6	μμf
Cathode to all other electrodes. . .	5	μμf
External conductive coating to ultor .	{ 1500 max. 1000 min.	{ μμf μμf
Electron Gun	Type Requiring No Ion-Trap Magnet	

Optical:

Faceplate and Protective Panel	Filterglass
Light transmission (Approx.)	44%
Phosphor (For Curves, see front of this Section) .	P4—Sulfide Type, Aluminized

Mechanical:

Operating Position	Any
Weight (Approx.)	18-1/2 lbs
Overall Length	11-5/8" ± 5/16"
Neck Length.	4-1/8" ± 1/8"
Projected Area of Screen	172 sq. in.
External Conductive Coating:	


Type	Regular Band
Contact area for grounding	Near Reference Line
For Additional Information on Coatings and Dimensions:	

See *Picture-Tube Dimensional-Outlines* and *Bulb J149 C* sheets at the front of this section

Cap	Recessed Small Cavity (JEDEC No.J1-21)
Base.	Small-Button Neoeightar 7-Pin, Arrangement 1 (JEDEC No.B7-208)

Basing Designation for BOTTOM VIEW 8HR

- Pin 1 - Heater
- Pin 2 - Grid No.1
- Pin 3 - Grid No.2
- Pin 4 - Grid No.4
- Pin 6 - Grid No.1
- Pin 7 - Cathode
- Pin 8 - Heater



- Cap - Ultor
- (Grid No.3,
- Grid No.5,
- Collector)
- C - External
- Conductive
- Coating



19AFP4

Maximum Ratings, *Design-Maximum Values:*

ULTOR VOLTAGE.	20000 max.	volts
GRID-No.4 (FOCUSING) VOLTAGE:		
Positive value	1100 max.	volts
Negative value	550 max.	volts
GRID-No.2 VOLTAGE.	550 max.	volts
GRID-No.1 VOLTAGE:		
Negative peak value.	220 max.	volts
Negative bias value.	155 max.	volts
Positive bias value.	0 max.	volts
Positive peak value.	2 max.	volts
PEAK HEATER-CATHODE VOLTAGE:		
Heater negative with respect to cathode:		
During equipment warm-up period not exceeding 15 seconds	450 max.	volts
After equipment warm-up period . . .	200 max.	volts
Heater positive with respect to cathode	200 max.	volts

Typical Operating Conditions:

<i>With ultor voltage of</i>	16000	volts
<i>and grid-No.2 voltage of</i>	300	volts
Grid-No.4 Voltage for focus.	0 to 400	volts
Grid-No.1 Voltage for visual extinction of focused raster.	-35 to -72	volts

Maximum Circuit Values:

Grid-No.1-Circuit Resistance	1.5 max.	megohms
--	----------	---------

For X-radiation shielding considerations, see sheet
X-RADIATION PRECAUTIONS FOR CATHODE-RAY TUBES
at front of this section