

Picture Tube

SHORT RECTANGULAR GLASS TYPE
LOW-VOLTAGE ELECTROSTATIC FOCUS

ALUMINIZED SCREEN
114° MAGNETIC DEFLECTION

With Heater Having Controlled Warm-Up Time

GENERAL DATA

Electrical:

Heater Current at 6.3 volts.	600 ± 60	ma
Heater Warm-Up Time (Average).	11	seconds
Direct Interelectrode Capacitances:		
Grid No.1 to all other electrodes. . .	6	μuf
Cathode to all other electrodes. . .	5	μuf
External conductive coating to ultor .	{ 2500 max. 1700 min.	{ μuf μuf
Electron Gun	Type Requiring No Ion-Trap Magnet	


Optical:

Faceplate.	Filterglass
Light transmission (Approx.)	78%
Phosphor (For curves, see front of this Section) .P4—Sulfide Type, Aluminized	

Mechanical:

Operating Position	Any
Weight (Approx.)	24 lbs
Overall Length	13-5/8" ± 5/16"
Neck Length.	4-3/8" ± 1/8"
Projected Area of Screen	282 sq. in.
External Conductive Coating:	
Type	Regular Band
Contact area for grounding	Near Reference Line
For Additional Information on Coatings and Dimensions:	
See <i>Picture-Tube Dimensional-Outlines</i> and <i>Bulb J187 B</i> sheets at the front of this section	
Cap.	Recessed Small Cavity (JEDEC No.J1-21)
Base	Small-Button Neoeightar 7-Pin, Arrangement 1 (JEDEC No.B7-208)
Basing Designation for BOTTOM VIEW	.8HR

Pin 1—Heater
Pin 2—Grid No.1
Pin 3—Grid No.2
Pin 4—Grid No.4
Pin 6—Grid No.1
Pin 7—Cathode
Pin 8—Heater



Cap—Ultor
(Grid No.3,
Grid No.5,
Collector)
C—External
Conductive
Coating



23FP4

Maximum and Minimum Ratings, Design-Maximum Values:

ULTOR VOLTAGE.	{ 22000 max. 11000 min.	volts volts
GRID-No.4 (FOCUSING) VOLTAGE:		
Positive value	1100 max.	volts
Negative value	550 max.	volts
GRID-No.2 VOLTAGE.	{ 550 max. 200 min.	volts volts
GRID-No.1 VOLTAGE:		
Negative peak value.	220 max.	volts
Negative bias value.	154 max.	volts
Positive bias value.	0 max.	volts
Positive peak value.	2 max.	volts
HEATER VOLTAGE	{ 6.9 max. 5.7 min.	volts volts
PEAK HEATER-CATHODE VOLTAGE:		
Heater negative with respect to cathode:		
During equipment warm-up period not exceeding 15 seconds	450 max.	volts
After equipment warm-up period . . .	200 max.	volts
Heater positive with respect to cathode	200 max.	volts

Typical Operating Conditions:

<i>With ultor voltage of</i>	14000	volts
<i>and grid-No.2 voltage of</i>	450	volts
Grid-No.4 Voltage for focus.	0 to 400	volts
Grid-No.1 Voltage for visual extinction of focused raster	-45 to -105	volts

Maximum Circuit Values:

Grid-No.1-Circuit Resistance	1.5 max.	megohms
--	----------	---------

For X-radiation shielding considerations, see sheet
 X-RADIATION PRECAUTIONS FOR CATHODE-RAY TUBES
 at front of this section

